

**KEMET Part Number: C1812C475K5RACTU**  
(C1812C475K5RAC7800)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Class II, 4.7 uF, +/-10% Tol, 50 V, X7R, 1812 (4532 metric)



CeramicChipSMDNoS  
© 2011 KEMET Corp.  
All rights reserved

#### General Information

Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1812 (4532 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, Temperature Stable, Class II
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

#### Dimensions (mm)

Symbol	Dimension	Tolerance
L	4.5	+/-0.3
W	3.2	+/-0.3
T	1.6	+/-0.20
B	0.6	+/-0.35

#### Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	1000

#### Specifications

Capacitance:	4.7 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	110 MOhm
Dielectric Strength:	125 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours