

KEMET Part Number: T541X107M025AH6510
(04052-060)



Capacitor, Tantalum, 100 uF, 7343, +/-20% Tol, 25 VDC (85C), Failure Rate=A (Non-ER)



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	4	+/-0.3
F	2.4	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	1.7	REF
R	1	REF
T	0.13	REF
A	3.8	MIN
G	3.5	REF
E	3.5	REF

Notes:

-In polarity stripe, at KEMET's option, type may be indicated: no symbol = Standard (or low leakage) MnO2 tantalum chip, O = LowESR T494, R = Low ESR T495, F = Fused T496, HT = 150C rated T498 (or B45196P, B45198P), H = 175C rated T499, H2 = 200C rated T50

General Information	
Supplier:	KEMET
Application:	Military COTS/Low ESR
Sub Application:	(MultipleAnode/ NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, COTS, Multi-Anode, Low ESR
Construction:	Multiple Anode Chip-Polymer
Body Type:	SMD Chip
Termination:	Solder Coated
Footprint:	7343
Weight:	410.89 mg
Approvals:	DLA Drawing 04052
RoHS:	No

Specifications	
Capacitance:	100 uF
Tolerance:	+/-20%
Voltage:	25 VDC (85C)
Voltage:	16.75 VDC (125C)
Temperature Range:	-55/+125C
Testing:	4 Cycles At +25C +/-5C Before Voltage Aging
Current/Ripple Current:	2121 mA (45C)
Resistance/ESR:	60 mOhms (100kHz 25C)
Failure Rate:	A (Non-ER)
Leakage Current:	250 uA
Dissipation Factor:	10%

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2016 IntelliData.net