


Capacitor, Tantalum, 330 uF, 7343, +/-20% Tol, 2.5 VDC (105C), Failure Rate=A (Non-ER)



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	1.9	+/-0.1
F	2.4	+/-0.1
S	1.3	+/-0.3
X	0.05	REF
T	0.13	REF
A	3.8	MIN
G	3.5	REF
E	3.5	REF

**Notes:**

-In Polarity Stripe, At KEMET's Option, Type May Be Indicated:  
 No Symbol = Standard MnO2 Tantalum Chip, O = Low ESR T494, R = Low ESR T495, F = Fused T496, HT = 150C Rated T498 (or B45196P, B45198P), H = 175C Rated T499, M = Multiple Anode Construction T51

General Information	
Supplier:	KEMET
Application:	Military COTS/Upscreened/Low ESR (Non-ER)
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, COTS, Low Profile, Up Screen
Construction:	Standard Chip-Polymer
Body Type:	SMD Chip
Termination:	Solder Coated
Footprint:	7343
Weight:	262.9 mg
RoHS:	No

Specifications	
Capacitance:	330 uF
Tolerance:	+/-20%
Voltage:	2.5 VDC (105C)
Temperature Range:	-55/+105C
Testing:	Standard Testing Only
Current/Ripple Current:	2735 mAmps (100kHz 45C)
Resistance/ESR:	25 mOhms (100kHz)
Failure Rate:	A (Non-ER)
Leakage Current:	82.5 uA
Dissipation Factor:	10%

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	1000