

Capacitor, Tantalum, 22 uF, +/-10% Tol, 35 V

**General Information**

<b>Supplier:</b>	KEMET
<b>Application:</b>	General Purpose
<b>Body Type:</b>	Axial Hermetic
<b>Lead Type:</b>	Un-insulated Wire
<b>Termination Type:</b>	Tin (Sn)
<b>RoHS:</b>	Yes

**Specifications**

<b>Capacitance:</b>	22 uF
<b>Tolerance:</b>	+/-10%
<b>Voltage:</b>	35 VDC (85C)
<b>Voltage:</b>	28 VDC (125C Surge)
<b>Voltage:</b>	0.35 V (125C Reverse)
<b>Temperature Range:</b>	-55/+125C
<b>Resistance/ESR:</b>	1.3 Ohms (100kHz)
<b>Leakage Current:</b>	4 uA
<b>Dissipation Factor:</b>	4%

**Dimensions (mm)**

Symbol	Dimension	Tolerance
D	7.34	+/-0.25
L	17.42	+/-0.79
L2	20.88	
F	0.64	+/-0.05
LL	38.1	+/-6.35

Notes:

-When Supplied On T&R Or Ammo, Lead Length Is Determined By Taping Specification

**Packaging Specifications**

<b>Package Kind:</b>	Bulk
<b>Package Type:</b>	Tray
<b>Package Quantity:</b>	20