

Capacitor, Ceramic, SMD, MLCC, High Temp, Ultra-Stable, Low Loss, 2200 pF, +/-5% Tol, 100 V, COG, 0603 (1608 metric)



General Information	
Supplier:	KEMET
Application:	200C
Chip Size:	0603 (1608 metric)
Temperature Coefficient:	COG
Part Type Description:	SMD, MLCC, High Temp, Ultra-Stable, Low Loss
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.6	+/-0.15
W	0.8	+/-0.15
T	0.8	+/-0.07
B	0.35	+/-0.15
S	0.7	MIN

Specifications	
Capacitance:	2200 pF
Voltage:	100 V
Tolerance:	+/-5%
Temperature Range:	-55/+200C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	100 GOhm
Dielectric Strength:	250 V

Packaging Specifications	
Package Kind:	Cut Reel
Package Quantity:	500