


KEMET Part Number: C1206V223KBRACU
(C1206V223KBRAC7800)



Capacitor, Ceramic, SMD, MLCC, Arcshield, High Voltage, Temp Stable, 0.022 uF, +/-10% Tol, 630 V, X7R, 1206 (3216 metric)



CeramicChipSolutions
© 2016 KEMET Inc.
All rights reserved

General Information	
Supplier:	KEMET
Application:	Arc Shield
Chip Size:	1206 (3216 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, Arcshield, High Voltage, Temp Stable
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
T	1.7	+/-0.20
B	0.5	+/-0.25

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2000

Specifications	
Capacitance:	0.022 uF
Voltage:	630 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	4.55 GOhm
Dielectric Strength:	945 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours
Miscellaneous:	X7R dielectric is not recommended for AC line filtering or pulse applications

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2016 IntelliData.net