


Capacitor, Tantalum, General Purpose Radial Conformal (Dipped), 47 uF, +/-10% Tol, 25 V, Lead Spacing=5.08 mm



Dimensions (mm)

Symbol	Dimension	Tolerance
D	8.9	
H	13.5	
F	0.5	+/-0.05
S	5.08	+/-0.38
LL	12.7	+/-1.26

Packaging Specifications

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100

General Information

Supplier:	KEMET
Application:	General Purpose
Part Type Description:	General Purpose Radial Conformal (Dipped)
Body Type:	Radial Conformal
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications

Capacitance:	47 uF
Tolerance:	+/-10%
Voltage:	25 V (85C)
Voltage:	21 VDC (125C Surge)
Voltage:	0.25 V (125C Reverse)
Temperature Range:	-55/+125C
Leakage Current:	9.4 uA
Dissipation Factor:	6%