

KEMET Part Number: C350C335K5R5TA
(C350C335K5R5TABULK)

Capacitor, ceramic, 3.3 uF, +/-10% Tol, 50 V, X7R, Lead Spacing=0.4"



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	8.38	MAX
H	8.13	MAX
T	5.08	MAX
S	10.16	NOM
LL	7	MIN
F	0.64	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	50

General Information	
Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	X7R
Body Type:	Radial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

Specifications	
Capacitance:	3.3 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Failure Rate:	N/A
Dissipation Factor:	2.5%
Insulation Resistance:	150 MOhm
Dielectric Strength:	125 V