

KEMET Part Number: C0603C104J3RACTU
(C0603C104J3RAC7867)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Class II, 0.1 uF, +/-5% Tol, 25 V, X7R, 0603 (1608 metric)



| General Information | |
|--------------------------|---|
| Supplier: | KEMET |
| Application: | Standard Chip |
| Chip Size: | 0603 (1608 metric) |
| Temperature Coefficient: | X7R |
| Part Type Description: | SMD, MLCC, Temperature Stable, Class II |
| Termination Type: | Tin (Sn) |
| Marked: | No |
| RoHS: | Yes |

| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 1.6 | +/-0.15 |
| W | 0.8 | +/-0.15 |
| T | 0.8 | +/-0.07 |
| B | 0.35 | +/-0.15 |
| S | 0.7 | MIN |

| Specifications | |
|------------------------|--|
| Capacitance: | 0.1 uF |
| Voltage: | 25 V |
| Tolerance: | +/-5% |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 3.5% |
| Failure Rate: | N/A |
| Aging Rate: | 3% loss/decade hour |
| Insulation Resistance: | 5 GOhm |
| Dielectric Strength: | 62.5 V |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 48 hours |

| Packaging Specifications | |
|--------------------------|-------------|
| Package Kind: | T&R |
| Package Size: | 7 in/180 mm |
| Package Type: | Paper Tape |
| Package Quantity: | 4000 |