

Capacitor, Ceramic, SMD, MLCC, FT-CAP, Auto Grade, 22 uF, +/-10% Tol, 25 V, X7R, 2220 (5750 metric)



General Information	
Supplier:	KEMET
Application:	Automotive (AEC-Q200 Qualified)
Chip Size:	2220 (5750 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, FT-CAP, Auto Grade
Termination Type:	Flexible Termination
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	5.9	+/-0.75
W	5	+/-0.4
T	2.4	+/-0.15
B	0.7	+/-0.35

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	500

Specifications	
Capacitance:	22 uF
Voltage:	25 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Dissipation Factor:	3.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	20 MOhm
Dielectric Strength:	62.5 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours