

Capacitor, Ceramic, SMD, MLCC, FT-CAP, Ultra-Stable, Auto Grade, 18 pF, +/-5% Tol, 50 V, COG, 0603 (1608 metric)



General Information	
Supplier:	KEMET
Application:	Automotive (AEC-Q200 Qualified)
Chip Size:	0603 (1608 metric)
Temperature Coefficient:	COG
Part Type Description:	SMD, MLCC, FT-CAP, Ultra-Stable, Auto Grade
Termination Type:	Flexible Termination
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.6	+/-0.17
W	0.8	+/-0.15
T	0.8	+/-0.15
B	0.45	+/-0.15
S	0.58	MIN

Specifications	
Capacitance:	18 pF
Voltage:	50 V
Tolerance:	+/-5%
Temperature Range:	-55/+125C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	100 GOhm
Dielectric Strength:	125 V
Miscellaneous:	Note: KEMET 50V rated parts may be operated at 63 Volts

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Paper Tape
Package Quantity:	4000