

Capacitor, Ceramic, SMD, MLCC, Open Mode, Auto Grade, 2.2 uF, +/-10% Tol, 50 V, X7R, 1210 (3225 metric)



| General Information      |   |
|--------------------------|---|
| Supplier:                | KEMET                                     |
| Application:             | Automotive/Open Mode (AEC-Q200 Qualified) |
| Chip Size:               | 1210 (3225 metric)                        |
| Temperature Coefficient: | X7R                                       |
| Part Type Description:   | SMD, MLCC, Open Mode, Auto Grade          |
| Termination Type:        | Tin (Sn)                                  |
| Marked:                  | No  |
| RoHS:                    | Yes                                       |

| Dimensions (mm) |           |           |
|-----------------|-----------|-----------|
| Symbol          | Dimension | Tolerance |
| L               | 3.2       | +/-0.2    |
| W               | 2.5       | +/-0.2    |
| T               | 1.7       | +/-0.20   |
| B               | 0.5       | +/-0.25   |

| Packaging Specifications |              |
|--------------------------|--------------|
| Package Kind:            | T&R          |
| Package Size:            | 7 in/180 mm  |
| Package Type:            | Plastic Tape |
| Package Quantity:        | 2000         |

| Specifications         |  |
|------------------------|--|
| Capacitance:           | 2.2 uF   |
| Voltage:               | 50 V   |
| Tolerance:             | +/-10%   |
| Temperature Range:     | -55/+125C  |
| Dissipation Factor:    | 2.5%   |
| Failure Rate:          | N/A  |
| Aging Rate:            | 3% loss/decade hour  |
| Insulation Resistance: | 230 MOhm   |
| Dielectric Strength:   | 125 V  |
| Miscellaneous:         | Note: Referee time for X7R dielectric for this part number is 1000 hours |