


**KEMET Part Number: C330C153J1G5TA**  
(C330C153J1G5TABULK)

Capacitor, ceramic, 0.015 uF, +/-5% Tol, 100 V, C0G, Lead Spacing=0.2"



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	7.11	MAX
H	9.14	MAX
T	4.07	MAX
S	5.08	NOM
LL	7	MIN
F	0.51	NOM

**Packaging Specifications**

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	250

**General Information**

Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	C0G
Body Type:	Radial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

**Specifications**

Capacitance:	0.015 uF
Voltage:	100 V
Tolerance:	+/-5%
Temperature Range:	-55/+125C
Failure Rate:	N/A
Dissipation Factor:	0.1%
Insulation Resistance:	66.67 GOhm
Dielectric Strength:	250 V