


Capacitor, Tantalum, SMD, Polymer, Molded, Low ESR, Non-Combustible, 22 uF, 3216, +/-20% Tol, 6.3 VDC (105C)



#### General Information

Supplier:	KEMET
Application:	Low ESR
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible
Construction:	Standard Chip-Polymer
Body Type:	SMD Chip
Footprint:	3216
Weight:	53.16 mg
RoHS:	Yes

#### Dimensions (mm)

Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
H	1.6	+/-0.2
F	1.2	+/-0.1
S	0.8	+/-0.3
X	0.1	+/-0.1
P	0.4	REF
R	0.4	REF
T	0.13	REF
A	1.2	MIN

#### Specifications

Capacitance:	22 uF
Tolerance:	+/-20%
Voltage:	6.3 VDC (105C)
Temperature Range:	-55/+105C
Current/Ripple Current:	1100 mAmps (100kHz 45C)
Current/Ripple Current:	770 mAmps (85C)
Current/Ripple Current:	522.5 mAmps (105C)
Resistance/ESR:	90 mOhms (100kHz 25C)
Failure Rate:	N/A
Leakage Current:	13.9 uA
Dissipation Factor:	8%

#### Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	2000