

KEMET Part Number: PME271Y433MR30
(P271HH332M250A)

Capacitor, film, Metallized Paper, 3300 pF, +/-20% Tol, -40/+100C, Safety: Y2, 250 VAC, Lead Spacing=10.2 mm



Dimensions (mm)

Symbol	Dimension	Tolerance
L	13.5	MAX
H	8.2	MAX
T	4.1	MAX
S	10.2	+/-0.4
LL	30	+5
F	0.6	+/-0.05

Packaging Specifications

Package Kind:	Bulk
Package Quantity:	1000

General Information

Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Safety: Y2
Style:	Radial Molded
Lead Form:	Wire Leads
Features:	Pulse
Approvals:	ENEC,UL,cUL,CQC
RoHS:	Yes

Specifications

Capacitance:	3300 pF
Voltage:	1000 VDC
Tolerance:	+/-20%
Voltage AC:	250 VAC
Rated Temperature:	100C
Temperature Range:	-40/+100C
Dissipation Factor @ 1 kHz:	1.3%
Insulation Resistance:	12 GOhm
Maximum dVdT:	2000 v/us
Miscellaneous:	SRF= 30 MHz