

KEMET Part Number: PMR209MC6220M100R30
(P409CP224M250AH101)

Capacitor, film, Metallized Paper, 0.22 uF, +/-20% Tol, -40/+85C, Integrated Resistor (X2), 630 VDC@85C, Lead Spacing=20.3 mm, Not For New Design, Please Check Possible Alternative Parts (AltPart)



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	24	MAX
H	16.5	MAX
T	11.3	MAX
S	20.3	+/-0.4
LL	30	+5
F	0.8	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	150

General Information	
Supplier:	KEMET
Dielectric:	Metallized Paper
Application:	Integrated Resistor (X2)
Style:	Radial Molded
Lead Form:	Wire Leads
Features:	Pulse
RoHS:	Yes

Specifications	
Capacitance:	0.22 uF
Voltage:	630 VDC
Tolerance:	+/-20%
Voltage AC:	250 VAC
Rated Temperature:	85C
Temperature Range:	-40/+85C
Insulation Resistance:	3 GOhm
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart)
Miscellaneous:	Resistor= 100 Ohms