

KEMET Part Number: T495X107K016ATE100
(B45197A3107K509)

Capacitor, Tantalum, SMD, MnO2, Molded, Low ESR, 100 uF, 7343, +/-10% Tol, 16 VDC (85C)



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	4	+/-0.3
F	2.4	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	1.7	REF
R	1	REF
T	0.13	REF
A	3.6	MIN
G	3.5	REF
E	3.5	REF

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

General Information	
Supplier:	KEMET
Application:	Low ESR
Part Type Description:	SMD, MnO2, Molded, Low ESR
Construction:	Standard Chip-MnO2
Body Type:	SMD Chip
Footprint:	7343
Weight:	652.04 mg
RoHS:	Yes

Specifications	
Capacitance:	100 uF
Tolerance:	+/-10%
Voltage:	16 VDC (85C)
Voltage:	10.72 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	1285 mAmps (25C)
Current/Ripple Current:	1156.5 mAmps (85C)
Current/Ripple Current:	514 mAmps (125C)
Resistance/ESR:	100 mOhms (100kHz)
Failure Rate:	N/A
Leakage Current:	16 uA
Dissipation Factor:	8%