

KEMET Part Number: C1210C226K9PACTU
(C1210C226K9PAC7800)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Class II, 22 uF, +/-10% Tol, 6.3 V, X5R, 1210 (3225 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1210 (3225 metric)
Temperature Coefficient:	X5R
Part Type Description:	SMD, MLCC, Temperature Stable, Class II
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.3
W	2.5	+/-0.3
T	2.5	+/-0.30
B	0.5	+0.35/-0.25

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	1000

Specifications	
Capacitance:	22 uF
Voltage:	6.3 V
Tolerance:	+/-10%
Temperature Range:	-55/+85C
Dissipation Factor:	10%
Failure Rate:	N/A
Aging Rate:	4% loss/decade hour
Insulation Resistance:	0 mOhm
Dielectric Strength:	15.75 V
Miscellaneous:	Note: Referee time for X5R dielectric for this part number is 48 hours