


Capacitor, Tantalum, SMD, MnO2, Molded, Low Profile, 330 uF, 7343, +/-10% Tol, 6.3 VDC (85C)



General Information	
Supplier:	KEMET
Application:	General Purpose
Part Type Description:	SMD, MnO2, Molded, Low Profile
Construction:	Standard Chip-MnO2
Body Type:	SMD Chip
Footprint:	7343
Weight:	286.4 mg
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	2	MAX
F	2.4	+/-0.1
S	1.3	+/-0.3
X	0.05	REF
T	0.13	REF
A	3.6	MIN
G	3.5	REF
E	3.5	REF

Specifications	
Capacitance:	330 uF
Tolerance:	+/-10%
Voltage:	6.3 VDC (85C)
Voltage:	4.22 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	423 mAmps (25C)
Current/Ripple Current:	380.7 mAmps (85C)
Current/Ripple Current:	169.2 mAmps (125C)
Resistance/ESR:	0.7 Ohms (100kHz)
Failure Rate:	N/A
Leakage Current:	20.8 uA
Dissipation Factor:	8%

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	1000

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.