

KEMET Part Number: T491C106M025AT
(B45196H5106M309)

Capacitor, Tantalum, SMD, MnO2, Molded, 10 uF, 6032, +/-20% Tol, 25 VDC (85C)



Dimensions (mm)

Symbol	Dimension	Tolerance
L	6	+/-0.3
W	3.2	+/-0.3
H	2.5	+/-0.3
F	2.2	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	0.9	REF
R	1	REF
T	0.13	REF
A	2.9	MIN
G	2.8	REF
E	2.4	REF

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

General Information

Supplier:	KEMET
Application:	General Purpose
Part Type Description:	SMD, MnO2, Molded
Construction:	Standard Chip-MnO2
Body Type:	SMD Chip
Footprint:	6032
Weight:	224.48 mg
RoHS:	Yes

Specifications

Capacitance:	10 uF
Tolerance:	+/-20%
Voltage:	25 VDC (85C)
Voltage:	16.75 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	271 mAmps (25C)
Current/Ripple Current:	243.9 mAmps (85C)
Current/Ripple Current:	108.4 mAmps (125C)
Resistance/ESR:	1.5 Ohms (100kHz)
Failure Rate:	N/A
Leakage Current:	2.5 uA
Dissipation Factor:	6%