

Capacitor, Ceramic, SMD, MLCC, High Temperature, FT-Cap, 1.5 uF, +/-10% Tol, 50 V, X7R, 1812 (4532 metric)



General Information	
Supplier:	KEMET
Application:	175C
Chip Size:	1812 (4532 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, High Temperature, FT-Cap
Termination Type:	Flexible Termination
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	4.5	+/-0.4
W	3.2	+/-0.3
T	1.9	+/-0.20
B	0.7	+/-0.35

Specifications	
Capacitance:	1.5 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+175C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	670 MOhm
Dielectric Strength:	125 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1