

Capacitor, Ceramic, SMD, MLCC, Ultra-Stable, Low Loss, Auto Grade, 15 pF, +/-5% Tol, 25 V, COG, 0603 (1608 metric)



| General Information      |   |
|--------------------------|---|
| Supplier:                | KEMET   |
| Application:             | Automotive (AEC-Q200 Qualified)               |
| Chip Size:               | 0603 (1608 metric)                            |
| Temperature Coefficient: | COG   |
| Part Type Description:   | SMD, MLCC, Ultra-Stable, Low Loss, Auto Grade |
| Termination Type:        | Tin (Sn)                                      |
| Marked:                  | No  |
| RoHS:                    | Yes   |

| Dimensions (mm) |           |           |
|-----------------|-----------|-----------|
| Symbol          | Dimension | Tolerance |
| L               | 1.6       | +/-0.15   |
| W               | 0.8       | +/-0.15   |
| T               | 0.8       | +/-0.07   |
| B               | 0.35      | +/-0.15   |
| S               | 0.7       | MIN       |

| Specifications         |                     |
|------------------------|---------------------|
| Capacitance:           | 15 pF               |
| Voltage:               | 25 V                |
| Tolerance:             | +/-5%               |
| Temperature Range:     | -55/+125C           |
| Dissipation Factor:    | 0.1%                |
| Failure Rate:          | N/A                 |
| Aging Rate:            | 0% loss/decade hour |
| Insulation Resistance: | 100 GOhm            |
| Dielectric Strength:   | 62.5 V              |

| Packaging Specifications |             |
|--------------------------|-------------|
| Package Kind:            | T&R         |
| Package Size:            | 7 in/180 mm |
| Package Type:            | Paper Tape  |
| Package Quantity:        | 4000        |