

**KEMET Part Number: PHE840MR7220MR05R06L2**  
(F840RF225M275C)

Capacitor, film, Metallized Polypropylene, 2.2 uF, +/-20% Tol, -55/+105C, Safety: X2, 275 VAC, Lead Spacing=37.5 mm, Not For New Design, Please Check Possible Alternative Parts (AltPart)



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	41	MAX
H	24	MAX
T	13	MAX
S	37.5	+/-0.5
LL	6	NOM
F	1	NOM

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Tray
Package Quantity:	140

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Safety: X2
Style:	Radial Box
Lead Form:	Wire Leads
Features:	Pulse
Approvals:	ENEC,UL,cUL
RoHS:	Yes

Specifications	
Capacitance:	2.2 uF
Voltage:	760 VDC
Tolerance:	+/-20%
Voltage AC:	275 VAC
Rated Temperature:	105C
Temperature Range:	-55/+105C
Dissipation Factor @ 1 kHz:	0.1%
Dissipation Factor @ 10 kHz:	0.8%
Insulation Resistance:	4.55 GOhm
Maximum dVdT:	100 v/us
Miscellaneous:	Not For New Design, Please Check Possible Alternative Parts (AltPart)