

**KEMET Part Number: C1206C104K3RACTU**  
(C1206C104K3RAC7800)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Class II, 0.1 uF, +/-10% Tol, 25 V, X7R, 1206 (3216 metric)



**General Information**

<b>Supplier:</b>	KEMET
<b>Application:</b>	Standard Chip
<b>Chip Size:</b>	1206 (3216 metric)
<b>Temperature Coefficient:</b>	X7R
<b>Part Type Description:</b>	SMD, MLCC, Temperature Stable, Class II
<b>Termination Type:</b>	Tin (Sn)
<b>Marked:</b>	No
<b>RoHS:</b>	Yes

**Dimensions (mm)**

Symbol	Dimension	Tolerance
<b>L</b>	3.2	+/-0.2
<b>W</b>	1.6	+/-0.2
<b>T</b>	0.78	+/-0.10
<b>B</b>	0.5	+/-0.25

**Packaging Specifications**

<b>Package Kind:</b>	T&R
<b>Package Size:</b>	7 in/180 mm
<b>Package Type:</b>	Plastic Tape
<b>Package Quantity:</b>	4000

**Specifications**

<b>Capacitance:</b>	0.1 uF
<b>Voltage:</b>	25 V
<b>Tolerance:</b>	+/-10%
<b>Temperature Range:</b>	-55/+125C
<b>Dissipation Factor:</b>	3.5%
<b>Failure Rate:</b>	N/A
<b>Aging Rate:</b>	3% loss/decade hour
<b>Insulation Resistance:</b>	10 GOhm
<b>Dielectric Strength:</b>	62.5 V
<b>Miscellaneous:</b>	Note: Referee time for X7R dielectric for this part number is 1000 hours