

Capacitor, Tantalum, SMD, Polymer, Molded, Low ESR, Non-Combustible, 47 uF, 7343, +/-20% Tol, 16 VDC (105C)



General Information	
Supplier:	KEMET
Application:	Low ESR
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible
Construction:	Standard Chip-Polymer
Body Type:	SMD Chip
Footprint:	7343
Weight:	434.83 mg
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	2.8	+/-0.3
F	2.4	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	0.9	REF
R	1	REF
T	0.13	REF
A	3.6	MIN

Specifications	
Capacitance:	47 uF
Tolerance:	+/-20%
Voltage:	16 VDC (105C)
Temperature Range:	-55/+105C
Current/Ripple Current:	1800 mAmps (100kHz 45C)
Current/Ripple Current:	1260 mAmps (85C)
Current/Ripple Current:	855 mAmps (105C)
Resistance/ESR:	70 mOhms (100kHz 25C)
Failure Rate:	N/A
Leakage Current:	75.2 uA
Dissipation Factor:	10%
Miscellaneous:	Not recommended for new designs. Please use the T521 version of this part.

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500