

KEMET Part Number: C1206C225K4RACTU
(C1206C225K4RAC7800)

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Class II, 2.2 uF, +/-10% Tol, 16 V, X7R, 1206 (3216 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1206 (3216 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, Temperature Stable, Class II
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.2	+/-0.2
W	1.6	+/-0.2
T	1.6	+/-0.20
B	0.5	+/-0.25

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	2000

Specifications	
Capacitance:	2.2 uF
Voltage:	16 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Dissipation Factor:	3.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	230 MOhm
Dielectric Strength:	40 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 48 hours