


KEMET Part Number: ALT22A153DE063



Capacitor, aluminum, 0.015 F, +/-20% Tol, -40/+85C, 63 VDC@85C



General Information	
Supplier:	KEMET
Application:	General Purpose
Part Type Description:	Solder Tag, Aluminum Electrolytic
Lead Type:	2 Flying leads (solder tags)
Weight:	125 g
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
D	40	+/-1
L	75	+/-2
S	10	+/-0.1
LL	10	+/-0.5

Specifications	
Capacitance:	0.015 F
Voltage:	63 VDC
Tolerance:	+/-20%
Voltage:	72.45 VDC (Surge)
Rated Temperature:	85C
Temperature Range:	-40/+85C
Life:	26000 Hrs
Leakage Current:	5.67 mA
Leakage Condition:	uAmps (5min 20C)

Notes:
-Dimensions D And L Include Slewing

Packaging Specifications	
Package Kind:	Bulk

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.



© 2006-2016 IntelliData.net