



## SAFETY DATA SHEET

### 3 IN ONE SILICONE LUBRICANT

#### 1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/UNDERTAKING

PRODUCT NAME 3 IN ONE SILICONE LUBRICANT  
 SUPPLIER WD-40 Company Limited  
 PO Box 440  
 Kiln Farm  
 Milton Keynes  
 MK11 3LF  
 Tel: 01908 555400  
 Fax: 01908 266900

#### 2 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
(L) ORANGE TERPENES		5989-27-5	< 1%	Xn;R65. Xi;R38. N;R50/53. R10.
BUTANE	203-448-7	106-97-8	10-30%	F+;R12
DISTILLATES (PETROLEUM) HYDROTREATED LIGHT	265-149-8	64742-47-8	30-60%	Xn;R65. R66.
NAPHTHA (PETROLEUM) HYDROTREATED HEAVY	265-150-3	64742-48-9	10-30%	Xn;R65. R10,R66,R67.

The Full Text for all R-Phrases are Displayed in Section 16

#### 3 HAZARDS IDENTIFICATION

Extremely flammable. Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness.

CLASSIFICATION F+;R12. R66, R67.

#### 4 FIRST-AID MEASURES

##### INHALATION

Move the exposed person to fresh air at once. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Keep the affected person warm and at rest. Get prompt medical attention.

##### INGESTION

DO NOT INDUCE VOMITING! NEVER MAKE AN UNCONSCIOUS PERSON VOMIT OR DRINK FLUIDS! Immediately rinse mouth and drink plenty of water (200-300 ml). Get medical attention.

##### SKIN CONTACT

Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention promptly if symptoms occur after washing.

##### EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

#### 5 FIRE-FIGHTING MEASURES

##### EXTINGUISHING MEDIA

Use: Foam. Water spray, fog or mist. Dry chemicals, sand, dolomite etc.

##### SPECIAL FIRE FIGHTING PROCEDURES

Containers close to fire should be removed or cooled with water. Avoid water in straight hose stream; will scatter and spread fire. Keep run-off water out of sewers and water sources. Dike for water control.

##### UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

##### SPECIFIC HAZARDS

Fire or high temperatures create: Carbon monoxide (CO). Carbon dioxide (CO<sub>2</sub>).

##### PROTECTIVE MEASURES IN FIRE

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

#### 6 ACCIDENTAL RELEASE MEASURES

**3 IN ONE SILICONE LUBRICANT****PERSONAL PRECAUTIONS**

Wear protective clothing as described in Section 8 of this safety data sheet.

**ENVIRONMENTAL PRECAUTIONS**

Avoid discharge to the aquatic environment.

**SPILL CLEAN UP METHODS**

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb with inert, damp, non-combustible material, then flush area with water. Do not let washing down water contaminate ponds or waterways. Containers with collected spillage must be properly labelled with correct contents and hazard symbol.

**7 HANDLING AND STORAGE****USAGE PRECAUTIONS**

Keep away from heat, sparks and open flame. Avoid inhalation of vapours/spray and contact with skin and eyes.

**STORAGE PRECAUTIONS**

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

**8 EXPOSURE CONTROLS/PERSONAL PROTECTION**

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3

**INGREDIENT COMMENTS**

WEL = Workplace Exposure Limits

**PROTECTIVE EQUIPMENT****ENGINEERING MEASURES**

Provide adequate ventilation. Observe Workplace Exposure Limits and minimise the risk of inhalation of vapours.

**HAND PROTECTION**

Wear protective gloves. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

**EYE PROTECTION**

Wear approved chemical safety goggles where eye exposure is reasonably probable.

**HYGIENE MEASURES**

DO NOT SMOKE IN WORK AREA! Promptly remove any clothing that becomes contaminated. Wash promptly if skin becomes contaminated. When using do not eat, drink or smoke.

**9 PHYSICAL AND CHEMICAL PROPERTIES**

APPEARANCE	Aerosol
COLOUR	Clear
SOLUBILITY	Insoluble in water
FLASH POINT (°C)	-28.9°C TOC (Tag open cup).

**10 STABILITY AND REACTIVITY****STABILITY**

Stable under normal temperature conditions and recommended use.

**CONDITIONS TO AVOID**

Aerosol cans: Must not be exposed to direct sunlight or temperatures above 50°C.

**MATERIALS TO AVOID**

Strong oxidising substances. Strong alkalis. Strong acids.

**HAZARDOUS DECOMPOSITION PRODUCTS**

During fire, toxic gases (CO, CO<sub>2</sub>) are formed.

**11 TOXICOLOGICAL INFORMATION****INHALATION**

Vapours may cause drowsiness and dizziness.

**INGESTION**

May cause discomfort if swallowed. May cause stomach pain or vomiting. Gastrointestinal symptoms, including upset stomach.

**3 IN ONE SILICONE LUBRICANT****SKIN CONTACT**

Repeated exposure may cause skin dryness or cracking.

**EYE CONTACT**

Spray and vapour in the eyes may cause irritation and smarting.

**12 ECOLOGICAL INFORMATION****ECOTOXICITY**

Not regarded as dangerous for the environment.

**13 DISPOSAL CONSIDERATIONS****DISPOSAL METHODS**

Dispose of waste and residues in accordance with local authority requirements. Make sure containers are empty before discarding (explosion risk).

**14 TRANSPORT INFORMATION**

UK ROAD CLASS	2.1		
PROPER SHIPPING NAME	AEROSOLS		
UN NO. ROAD	1950	UK ROAD PACK GR.	#
ADR CLASS NO.	2.1	ADR CLASS	Class 2: Gases
ADR PACK GROUP	#	ADR LABEL NO.	2.1
CEFIC TEC(R) NO.	20G5F	RID CLASS NO.	2.1
RID PACK GROUP	#	UN NO. SEA	1950
IMDG CLASS	2.1	IMDG PACK GR.	#
EMS	F-D, S-U	MARINE POLLUTANT	No.
UN NO. AIR	1950	AIR CLASS	2.1
AIR PACK GR.	#		

**15 REGULATORY INFORMATION****LABELLING**

Extremely Flammable

**RISK PHRASES**

R12	Extremely flammable.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

**SAFETY PHRASES**

S2	Keep out of the reach of children
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S37	Wear suitable gloves.
S51	Use only in well-ventilated areas.
A1	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.

**STATUTORY INSTRUMENTS**

Control of Substances Hazardous to Health. Chemicals (Hazard Information and Packaging) Regulations.

**APPROVED CODE OF PRACTICE**

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

**3 IN ONE SILICONE LUBRICANT**

## GUIDANCE NOTES

CHIP for everyone HSG(108). Workplace Exposure Limits EH40.

**16 OTHER INFORMATION**

REVISION DATE 01-2006

REV. NO./REPL. SDS GENERATED 1 / 06-2003

## RISK PHRASES IN FULL

R10	Flammable.
R12	Extremely flammable.
R38	Irritating to skin.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

## DISCLAIMER

The information and recommendations contained in this safety data sheet represent, to the best of our knowledge and belief, an accurate and reliable representation as to the known data for this preparation at the date of issue. The information is intended only as a guide for safe handling, use, processing, storage and release and is not to be considered a warranty or quality specification. It is the responsibility of the user to evaluate this information in a prudent manner and to use it in a manner that is consistent for his/her particular purpose.