



## Harsh Environment Connectivity Solutions

---



### US Series, Front Mount, .620 Mounting Hole - Non-Illuminated

Cost-effective Uniswitch switches are non-lighted momentary switches featuring snap-in mounting in a single hole and a choice of solder/screw (#5-40), solder/quick-connect (AMP FASTON® 110) 60967-1, or stand-off PC terminals. Molded housing protects internal parts, and bezel functions as built-in escutcheon. Series LUS excepts T1 3/4 lamp (not included).

---

## MOUNTING

"Snap-in" mounting is in .617 (15.67 mm) inch minimum square hole - for row or matrix mounting. Panel thickness: .047 inch (1.19 mm) to .266 inch (6.76 mm) maximum. To mount, simply press switch into panel; "Adjusto-Clip" locking tabs engage panel and hold switch securely. Behind panel distance is 1.312 inch (33.32 mm) minimum.

## SPECIFICATIONS

**Switch Housing:** Molded plastic, charcoal gray only.

**"Adjusto-Clip":** Copper alloy.

**Contactors:** Copper alloy plated. Form 1-A rated:

250 mA, 30 W maximum, AC, non-inductive load.

**Terminals:** Copper alloy, silver-plated.

**Pushbuttons:** Molded plastic in 7 colors.

**Operating Force:** 12 - 16 ounce (340-454 grams).

## "ADJUSTO-CLIP" MOUNTING

Position Number	Panel Thickness Inch (mm)		Position Number	Panel Thickness Inch (mm)	
	Min.	Max.		Min.	Max.
1*	.047 (1.2)	.078 (2.0)	4	.188 (4.8)	.219 (5.6)

2	.094 (2.4)	.125 (3.2)	5	.234 (6.0)	.266 (6.8)
3	.141 (3.6)	.172 (4.4)			

\* "Adjusto-Clips" normally installed in this position unless otherwise specified.

\*\*\*Note: Lamp not included, pushbutton ordered seperately from the switch