

15 Amp Heavy Duty Hospital-Grade Outlet Strip *1584H* Series



Features

- Featuring a sturdy aluminum extruded case with a distinctive black powder paint coated steel cover.
- Designed to meet the special requirements for institutional and chronic care use.
- With "Hospital Grade" white receptacles, line cord and plug.
- Exceeds NEMA requirements for low leakage ground return and for withstanding impact or continuous physical shock without loss of grounding path continuity when plugged into properly grounded source receptacles.
- The white "Hospital Grade" receptacles are securely fastened onto the housing and interconnected with solidly bonded bus bars. All bus bars are double connected with a convection pressure sensitive clamp and safety screw.
- **Perfect for ground sensitive audio applications!**
- An additional grounding stud is provided on the case for any further external grounding requirements.
- Mounting feet (with keyhole slots) allow temporary work station mounting if desired.

Specifications

- Heavy duty 14 gauge cord - 14/3 SJT for extreme temperature ranges and integral clear molded "Hospital Grade" plug.
- Receptacles are NEMA 5-15R-HG.
- Complete with a 15 amp, 125 volt resettable circuit breaker to prevent accidental line overload.
- CSA certified, Standards C22.2 (No. 21-95 and No. 42-99), CSA Cord Sets No. 8 (Hospital Grade Powerbars).
- TUVus certified to UL60601-1 (medical grade) and UL 1363 (relocatable power taps).

Accessories

- Rack Cabinet Vertical Mount Adaptor

Part No.	Overall Dimensions			Outlets	Cord Length (ft)
	Height	Width	Length		
1584T4DH6	2.33	2.12	10.18	4	6
1584T4DH	2.33	2.13	13.36	4	12
1584T6DH6	2.33	2.12	13.36	6	6
1584T6DH	2.33	2.13	13.36	6	12
1584T8DH6	2.33	2.12	16.51	8	6
1584T8DH	2.33	2.13	16.51	8	12

Data subject to change without notice

© 2016. Hammond Manufacturing Ltd. All rights reserved.