

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0346916122](#)  
**Status:** **Active**  
**Overview:** Stac64™ Single, Multi-Pocket and Hybrid Header System  
**Description:** Stac64™ Right Angle Header Assembly, Plastic Pin-Alignment-Plate, 12 Circuits, Polarization C, Brown, Tray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34729-020 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-34729-020 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**

Product Family	PCB Headers
Series	<a href="#">34691</a>
Application	Power, Wire-to-Board
Comments	Polarization C
Overview	<a href="#">Stac64™ Single, Multi-Pocket and Hybrid Header System</a>
Product Literature Order No	987650-4561
Product Name	Stac64™
UPC	887191003665

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Brown
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.472/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	10.0A
Voltage - Maximum	500V

**EU ELV**  
**Compliant**

**EU RoHS** **China RoHS**  
**Compliant**

**REACH SVHC**  
Contained Per -  
ED/79/2015 (17  
December 2015)  
N,N-  
dimethylacetamide  
Boric acid

**Halogen-Free**  
**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Relevant
ELV	Compliant

**Search Parts in this Series**

[34691](#) Series

**Mates With**

[34729](#) 2.54mm (.100") Pitch Stac64™ Right Angle Receptacle, [31408](#) USCAR 2.54mm (.100") Pitch Receptacle

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-34729-020
Product Specification	PS-34729-020
Sales Drawing	SD-34691-601

This document was generated on 03/08/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**