



Datasheet for part number CA3108F24-11PYB15

|  |
|--|
| Our Catalog Part Number: CA3108F24-11PYB-15  |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |

|   |   |
|---|---|
| Product Datasheet                                   |   |
| Bayonet   | Connector with bayonet coupling   |
| Shell Style   | Plug, 90°   |
| Endbell Style                                       | Shielded connector with endbell for shielded braids and heat shrinkable boots   |
| Gender  | Pin   |
| Shell Size  | 24  |
| Contact Arrangement                                 | 24-11   |
| Number of contacts                                  | 3 contacts size 8, 6 contacts size 12   |
| Contact Type  | AWG Crimp   |
| Contact Plating                                     | Hard silver   |
| Shielding   | yes   |
| Insulator Rotation                                  | 250°  |
| Contact Rating at +20 °C (68 °F)<br>(Size 25/12)    | 41 A  |
| Contact Rating at +20 °C (68 °F)<br>(Size 60/100/8) | 74 A  |
| Contact Resistance (Size 25/12)                     | 3 mΩ  |
| Contact Resistance (Size 60/100/8)                  | 1 mΩ  |
| Wire Cross Section                                  | AWG 8 (Size 8 ), AWG 14/12 (Size 12)  |
| Operating Voltage                                   | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.  |
| Insulator Resistance                                | Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ |
| Test Voltage  | 2000 Vrms   |
| Air and Creepage Paths (Min)                        | 1,1 mm  |
| Ambient Temperature                                 | Standard insulator material -55°/+125°C (-67/257°F)   |
| Safety Provisions                                   | IP67 and IP68 (1 bar pressure after 12 hrs) acc. to DIN 40 050  |
| Salt Spray Resistance                               | 500 hours salt spray resistant  |
| Mating Cycles                                       | 500 min   |
| Sep. Force per Contact (Size 25/12)                 | 1,5 N   |
| Sep. Force per Contact (Size 60/100/8)              | 3,0 N   |
| Gage  | For infos on Gage please see catalog VG95234, part 1  |
| Coupling Torque                                     | Closing: 14 Nm max / Opening: 0,8 Nm min  |
| Contact Retention (Size 25/12)                      | 55 N  |
| Contact Retention (Size 60/100/8)                   | 80 N  |
| Shell Material                                      | Aluminium alloy   |
| Shell Plating                                       | Olive drab chromate over cadmium plating (conductive)   |
| Insulator and Grommet Material                      | CR-Elastomere   |
| Contact Material                                    | Copper alloy  |
| Harnessing Info: Contact Cross-Section              | <a href="#">See assembly instruction</a>  |
| Harnessing Info: Insulator Diameter                 | <a href="#">See assembly instruction</a>  |

Specifications and dimensions subject to change.



Datasheet for part number CA3108F24-11PYB15

|  |
|--|
| Our Catalog Part Number: CA3108F24-11PYB-15  |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |

|                                |   |
|--------------------------------|---|
| Product Datasheet              |   |
| Wire Stripping (Size 25/12)    | 6,2 mm  |
| Wire Stripping (Size 60/100/8) | 11,8 mm   |
| General Info                   | <i>All tests in accordance with VG95319 and/or if applicable with VG95210</i> |