

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0346900160](#)  
**Status:** **Active**  
**Overview:** [Stac64™ Single, Multi-Pocket and Hybrid Header System](#)  
**Description:** [Stac64™ Vertical Header Assembly, 16 Circuits, Polarization A, Black, Tray](#)

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-34729-020 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-34729-020 (PDF)</a>	<a href="#">Product Literature (PDF)</a>

**General**


Product Family	PCB Headers
Series	<a href="#">34690</a>
Application	Power, Wire-to-Board
Comments	Polarization A
Overview	<a href="#">Stac64™ Single, Multi-Pocket and Hybrid Header System</a>
Product Literature Order No	987650-4561
Product Name	Stac64™
UPC	883906122584

**Physical**

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Black
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	6.549/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.33mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +100°C
Termination Interface: Style	Through Hole

**Electrical**

Current - Maximum per Contact	10.0A
Voltage - Maximum	500V



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
ED/79/2015 (17  
December 2015)

N,N-  
dimethylacetamide

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Not Relevant

Compliant

**Search Parts in this Series**

[34690 Series](#)

**Mates With**

[34729 2.54mm \(.100"\) Pitch Stac64™ Right Angle Receptacle](#), [31408 USCAR 2.54mm \(.100"\) Pitch Receptacle](#)

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-34729-020
Product Specification	PS-34729-020
Sales Drawing	SD-34690-100

This document was generated on 04/04/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**