

Productname : PROPOWER FREEZER SPRAY
Ref.Nr.: UK10424-3-120606
Creationdate : 12.06.06
Replaces: 06.06.06

1. IDENTIFICATION OF PRODUCT AND COMPANY

Productname : PROPOWER FREEZER SPRAY
Aerosol

Application : Cooling agent

Company : PROPOWER Premier Farnell plc
150 Armley Road
LEEDS LS12 2QQ
Tel. : +44 (0) 870 129 8608
Fax :

In case of emergency : +44 (0) 870 202530

2. COMPOSITION AND INFORMATION ON COMPONENTS

Hazardous ingredient	CAS-nr	EINECS	w/w %	symbol	R-phrases*
dimethyl ether	115-10-6	204-065-8	5-10	F+	12
tetrafluoroethane	811-97-2	212-377-0	60-100	-	-

(* Explanation risk-phrases : see chapter 16)

3. HAZARD IDENTIFICATION

Health and Safety : Not Classified

Other hazards : Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.

4. FIRST AID MEASURES

General Advice : The usual precautions for handling chemicals should be observed

If any symptoms should occur, seek medical advice.

Contact with eyes : If substance has got into eyes, immediately wash out with plenty of water

Seek medical attention if irritation persists

Contact with skin : Wash with water and soap.

Seek medical attention if irritation persists

Inhalation : Fresh air, keep warm and at rest.

Ingestion : Ingestion is unlikely to occur

If swallowed accidentally, do not induce vomiting and seek medical advice.

5. FIRE-FIGHTING MEASURES

Flash point (without propellant): not available

Productname :	PROPOWER FREEZER SPRAY	Creationdate :	12.06.06
Ref.Nr.:	UK10424-3-120606	Replaces:	06.06.06

Explosion limits : upper limit : not available
lower limit : not available
Extinguishing media : foam, carbon dioxide or dry agent
Fire-fighting procedures : Keep container(s) exposed to fire cool, by spraying with water
Unusual exposure hazard : Aerosols may explode if heated above 50°C

6. ACCIDENTAL RELEASE MEASURES

Personal precautions : Shut off all ignition sources
 Ensure adequate ventilation
Environmental precautions : Do not allow to enter public sewers and watercourses
Cleaning methods : Absorb spillage in suitable inert material

7. HANDLING AND STORAGE

Handling procedures : Use only in well ventilated areas
 Do not pierce or burn aerosols, even after use.
 Do not spray on a naked flame or incandescent material.
 Do not breathe aerosols or vapours.
 Avoid contact with skin and eyes.
Storage procedures : Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
 Keep in a cool, dry, well ventilated place
 Keep out of reach of children.

8. EXPOSURE CONTROL AND PERSONAL PROTECTION

Control procedures : Ensure adequate ventilation
 Keep away from heat and sources of ignition
Personal protection : It is advisable to take precautions to avoid contact with skin and eyes when handling the product.
 Use only in well ventilated areas
inhalation : In case of insufficient ventilation, wear suitable respiratory equipment.
hands and skin : Wear suitable protective gloves
eyes : Wear safety goggles.
Exposure limits :

Hazardous ingredient	CAS-nr	method	
EU established exposure limits			
dimethyl ether	115-10-6	TWA	1000 ppm

9. PHYSICAL AND CHEMICAL PROPERTIES (for aerosols without propellant)

Apperance : physical state : liquified gas
colour : colourless

Productname :	PROPOWER FREEZER SPRAY	Creationdate :	12.06.06
Ref.Nr.:	UK10424-3-120606	Replaces:	06.06.06

odour :	Characteristic odour
Boiling point/range :	not available
Relative density :	not available
pH :	not available
Vapour pressure :	not available
Relative vapour density :	not available
Solubility in water :	Insoluble in water
Flash point :	not available
Auto-ignition :	not available
Viscosity :	not available
Evaporation rate :	not available

10. STABILITY AND REACTIVITY

Conditions to be avoided :	Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C. Keep away from heat and sources of ignition No hazardous reactions known if used for its intended purpose
Materials to be avoided :	Strong oxidising agent
Hazardous decomposition compounds :	carbon oxides

11. TOXICOLOGICAL INFORMATION

12. ECOLOGICAL INFORMATION

No experimental data available

13. WASTE DISPOSAL

National regulations :	Disposal should be in accordance with local, state or national legislation
-------------------------------	--

14. TRANSPORT

UN-number :	1950
Road/Rail - ADR/RID :	UN1950 Aerosols Class : 2, PG : NA, Class code : 5A, Label : 2.2
Sea - IMDG :	UN1950 Aerosols Ltd Qty Class : 2, PG : NA
EmS	F-D,S-U
Air - IATA/ICAO :	UN1950 Aerosols, non-flammable Class : 2.2, PG : NA, Label : RNG
Packing instr. LQ	Y203
PAX	203
CAO	203

Productname :	PROPOWER FREEZER SPRAY	Creationdate :	12.06.06
Ref.Nr.:	UK10424-3-120606	Replaces:	06.06.06

15. REGULATORY INFORMATION

Safety-phrase(s) : S2: Keep out of the reach of children.

Contains : 7 % by mass of the contents are flammable

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.

16. OTHER INFORMATION

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission.