

## RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




RJ45 connector, Degree of protection: IP20, Number of positions: 8, 1 Gbps, CAT5 (IEC 11801:2002), Material: PA, Connection method: IDC fast connection, Connection cross section: AWG 26-23, Cable exit: straight

### Why buy this product

- assembly without special tools
- UL
- GL
- Solid and stranded wires (1- and 7-wire)



### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 030045
Weight per Piece (excluding packing)	11.35 g
Custom tariff number	85366990
Country of origin	Switzerland

### Technical data

#### Mechanical characteristics

Number of positions	8
Connection profile	RJ45
Insertion/withdrawal cycles	≥ 1000
Connection method	IDC fast connection
Conductor cross section	0.13 mm <sup>2</sup> ... 0.32 mm <sup>2</sup> (solid) 0.14 mm <sup>2</sup> ... 0.36 mm <sup>2</sup> (stranded)
Connection cross section AWG	26 ... 23 (solid) 26 ... 23 (stranded)
Max. cable diameter	4.5 mm ... 8 mm
External cable diameter	4.5 mm ... 8 mm
Cable exit	straight

# RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725

## Technical data

### Mechanical characteristics

Color	traffic grey A RAL 7042
-------	-------------------------

### Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
---------------------------------	------------------

### Material data

Flammability rating according to UL 94	V0
Housing material	PA
Contact carrier material	PC
Contact material	Copper alloy
Contact surface material	Gold over nickel
Material	Plastic

### Electrical characteristics

Number of positions	8
Transmission speed	1 GBit/s
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
Rated current	1.75 A
Overvoltage category	I
Degree of pollution	1
Contact resistance	0.001 Ω (Wire – IDC) 0.005 Ω (Litz wires – IDC)

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260705
eCl@ss 7.0	27440312
eCl@ss 8.0	27440312

### ETIM

ETIM 2.0	EC000764
ETIM 3.0	EC001121
ETIM 4.0	EC001121
ETIM 5.0	EC002641

# RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725

## Classifications

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

#### Approvals

UL Listed / cUL Listed / GL / EAC / cULus Listed

---

#### Ex Approvals

---

#### Approvals submitted

---

## Approval details

UL Listed

cUL Listed

GL


EAC

cULus Listed


## Drawings

## RJ45 connector - VS-08-RJ45-5-Q/IP20 - 1656725

Dimensional drawing



Schematic diagram



RJ45 connector, IP20