

Productname :	PROPOWER SPRAY ADHESIVE	Creationdate :	12.06.06
Ref.Nr.:	UK10427-3-120606	Replaces:	06.06.06

1. IDENTIFICATION OF PRODUCT AND COMPANY

Productname : PROPOWER SPRAY ADHESIVE
Aerosol

Application : Adhesives

Company : PROPOWER Premier Farnell plc
150 Armley Road
LEEDS LS12 2QQ
Tel. : +44 (0) 870 129 8608
Fax :

In case of emergency : +44 (0) 870 202530

2. COMPOSITION AND INFORMATION ON COMPONENTS

Hazardous ingredient	CAS-nr	EINECS	w/w %	symbol	R-phrases*
methylcyclohexane	108-87-2	203-624-3	1-5	F,Xn,N	11-38-51/53-65-67
pentane	109-66-0	203-692-4	0-1	F+,Xn,N	12-51/53-65-66-67
cyclopentane	287-92-3	206-016-6	1-5	F	11-52/53
Naphtha (petroleum), hydrotreated light	64742-49-0	265-151-9	1-10	F,Xn,N	11-38-51/53-65-67
acetone; propan-2-one; propanone	67-64-1	200-662-2	10-30	F,Xi	11-36-66-67
Petroleum gases, liquefied	68476-85-7	270-704-2	30-60	F+	12
Naphtha (petroleum), hydrodesulfurized light, dearomatized	92045-53-9	295-434-2	0-15	F,Xn,N	11-38-51/53-65-67

(* Explanation risk-phrases : see chapter 16)

3. HAZARD IDENTIFICATION

Health and Safety : Extremely Flammable
Vapours may cause drowsiness and dizziness.

Environment : Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Other hazards : Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.

4. FIRST AID MEASURES

General Advice : The usual precautions for handling chemicals should be observed
If any symptoms should occur, seek medical advice.

Contact with eyes : If substance has got into eyes, immediately wash out with plenty of water

Productname :	PROPOWER SPRAY ADHESIVE	Creationdate :	12.06.06
Ref.Nr.:	UK10427-3-120606	Replaces:	06.06.06

Contact with skin : Wash with water and soap.
Seek medical attention if irritation persists

Inhalation : Fresh air, keep warm and at rest.

Ingestion : Ingestion is unlikely to occur
If swallowed accidentally, do not induce vomiting and seek medical advice.

5. FIRE-FIGHTING MEASURES

Flash point (without propellant): not available

Explosion limits : upper limit : not available

lower limit : not available

Extinguishing media : foam, carbon dioxide or dry agent

Fire-fighting procedures : Keep container(s) exposed to fire cool, by spraying with water

Unusual exposure hazard : Aerosols may explode if heated above 50°C

6. ACCIDENTAL RELEASE MEASURES

Personal precautions : Shut off all ignition sources
Ensure adequate ventilation

Environmental precautions : Do not allow to enter public sewers and watercourses

Cleaning methods : Absorb spillage in suitable inert material

7. HANDLING AND STORAGE

Handling procedures : Use only in well ventilated areas
Do not pierce or burn aerosols, even after use.
Do not spray on a naked flame or incandescent material.
Do not breathe aerosols or vapours.
Avoid contact with skin and eyes.

Storage procedures : Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep in a cool, dry, well ventilated place
Keep out of reach of children.

8. EXPOSURE CONTROL AND PERSONAL PROTECTION

Control procedures : Ensure adequate ventilation
Keep away from heat and sources of ignition

Personal protection : It is advisable to take precautions to avoid contact with skin and eyes when handling the product.
Use only in well ventilated areas

inhalation : In case of insufficient ventilation, wear suitable respiratory equipment.

hands and skin : Wear suitable protective gloves

Productname : PROPOWER SPRAY
ADHESIVE
Creationdate : 12.06.06
Ref.Nr.: UK10427-3-120606
Replaces: 06.06.06

eyes : Wear safety goggles.

Exposure limits :

Hazardous ingredient	CAS-nr	method	
EU established exposure limits			
acetone; propan-2-one; propanone	67-64-1	TWA	500 ppm

9. PHYSICAL AND CHEMICAL PROPERTIES (for aerosols without propellant)

Apperance : physical state : Liquid under pressure
colour : yellow
odour : Characteristic odour
Boiling point/range : not available
Relative density : not available
pH : not available
Vapour pressure : not available
Relative vapour density : not available
Solubility in water : Insoluble in water
Flash point : not available
Auto-ignition : not available
Viscosity : not available
Evaporation rate : not available

10. STABILITY AND REACTIVITY

Conditions to be avoided : Pressurized container : protect from sunlight and do not expose to temperatures exceeding 50°C.
Keep away from heat and sources of ignition
No hazardous reactions known if used for its intended purpose
Materials to be avoided : Strong oxidising agent
Hazardous decomposition compounds : carbon oxides

11. TOXICOLOGICAL INFORMATION

Inhalation : Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion : Ingestion is unlikely to occur
After vomiting of swallowed product aspiration into lungs is likely. Solvents may induce chemical pneumonia.
Skin contact : Irritating to skin
Other information: No experimental data available

Productname :	PROPOWER SPRAY ADHESIVE	Creationdate :	12.06.06
Ref.Nr.:	UK10427-3-120606	Replaces:	06.06.06

12. ECOLOGICAL INFORMATION

Other adverse effects : Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
No experimental data available

13. WASTE DISPOSAL

National regulations : Disposal should be in accordance with local, state or national legislation

14. TRANSPORT

UN-number :	1950
Road/Rail - ADR/RID :	UN1950 Aerosols Class : 2, PG : NA, Class code : 5F, Label : 2.1
Sea - IMDG :	UN1950 Aerosols Ltd Qty Class : 2, PG : NA
EmS	F-D,S-U
Air - IATA/ICAO :	UN1950 Aerosols, non-flammable Class : 2.2, PG : NA, Label : RNG
Packing instr. LQ	Y203
PAX	203
CAO	203

15. REGULATORY INFORMATION

Warning symbol(s) : F+

Risk-phrase(s) : R12: Extremely flammable.
R52/53: Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67: Vapours may cause drowsiness and dizziness.

Safety-phrase(s) : S2: Keep out of the reach of children.
S16: Keep away from sources of ignition - No smoking.
S23: Do not breathe spray.
S51: Use only in well-ventilated areas.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Do not spray on a naked flame or any incandescent material.

Productname :	PROPOWER SPRAY ADHESIVE	Creationdate :	12.06.06
Ref.Nr.:	UK10427-3-120606	Replaces:	06.06.06

16. OTHER INFORMATION

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties.

Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission.

***Explanation risk-phrases:**

R11: Highly flammable.

R12: Extremely flammable.

R38: Irritating to skin.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65: Harmful: may cause lung damage if swallowed.

R67: Vapours may cause drowsiness and dizziness.