

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1718573003](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: 2.54mm Pitch, KK® 254 RPC Wire-to-Board Right-Angle Header with Friction Lock, Tin (Sn) Plating, Tape and Reel, 3 Circuits

Documents:

3D Model	Test Summary TS-171856-0001 (PDF)
Drawing (PDF)	Test Summary TS-171857-0001 (PDF)
Product Specification PS-171856-0001 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-171856-0002 (PDF)	



Series image - Reference only

General

Product Family	PCB Headers
Series	171857
Application	Power, Signal, Wire-to-Board
Overview	KK® Interconnect System - Molex
Product Name	KK® 254
UPC	887191716206

Physical

Breakaway	No
Circuits (Loaded)	3
Circuits (maximum)	2
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Nickel
Material - Resin	High Temperature Thermoplastic
Net Weight	0.386/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Plating min - Mating	1.524µm
Polarized to Mating Part	Yes
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	030
Lead-free Process Capability	SMC&WAVE

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[171857 Series](#)

Mates With

[4455](#) , [2695](#) , [6471](#)

Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

Material Info

Reference - Drawing Numbers

Product Specification	PS-171856-0001, PS-171856-0002
Sales Drawing	SD-171857-0001
Test Summary	TS-171856-0001, TS-171857-0001

This document was generated on 03/31/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION