


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5040500791](#)  
**Status:** **Active**  
**Overview:** Pico-Lock™ Connector System  
**Description:** 1.50mm Pitch Pico-Lock™ Surface Mount Wire-to-Board Header, Right Angle, 2.00mm Mated Height, Positive Side Locks, 7 Circuits

**Documents:**

|   |   |
|---|---|
| <a href="#">3D Model</a>                                  | <a href="#">Application Specification AS-504051-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                             | <a href="#">Application Specification AS-504051-002 (PDF)</a> |
| <a href="#">Product Specification PS-504051-001 (PDF)</a> | <a href="#">Packaging Specification SPK-504050-001 (PDF)</a>  |
| <a href="#">Product Specification PS-504051-002 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>          |



**Agency Certification**

UL E29179

**General**

|                |   |
|----------------|---|
| Product Family | PCB Headers                                 |
| Series         | <a href="#">504050</a>                      |
| Application    | Wire-to-Board                               |
| Overview       | <a href="#">Pico-Lock™ Connector System</a> |
| Product Name   | Pico-Lock™                                  |
| UPC            | 884982939851                                |

**Physical**

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | No                             |
| Circuits (Loaded)              | 7                              |
| Circuits (maximum)             | 7                              |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 30                             |
| First Mate / Last Break        | No                             |
| Glow-Wire Compliant            | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | N/A                            |
| Lock to Mating Part            | Yes                            |
| Material - Metal               | Copper Alloy                   |
| Material - Plating Mating      | Gold over Nickel               |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 176.580/mg                     |
| Number of Rows                 | 1                              |
| Orientation                    | Right Angle                    |
| Packaging Type                 | Adhesive Tape on Reel          |
| Pitch - Mating Interface       | 1.50mm                         |
| Surface Mount Compatible (SMC) | Yes                            |
| Temperature Range - Operating  | -40°C to +105°C                |
| Termination Interface: Style   | Surface Mount                  |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 3.0A |
| Voltage - Maximum             | 150V |

**Material Info**

**Reference - Drawing Numbers**

|                           |                              |
|---------------------------|------------------------------|
| Application Specification | AS-504051-001, AS-504051-002 |
| Packaging Specification   | SPK-504050-001               |
| Product Specification     | PS-504051-001, PS-504051-002 |
| Sales Drawing             | SD-504050-001, SD-504050-002 |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS

ELV

China RoHS

Green Image  
Not Relevant

**Search Parts in this Series**

[504050 Series](#)

**Mates With**

[504051](#) Pico-Lock™ Crimp Housing

This document was generated on 03/30/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**