

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0026605120](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** KK® 396 Header, Right-Angle with Friction Lock, 12 Circuits, Tin (Sn) Plating

**Documents:**

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| <a href="#">3D Model</a>      | <a href="#">Product Specification PS-08-50 (PDF)</a> |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                                 |
|----------------|-------------------------------------------------|
| Product Family | PCB Headers                                     |
| Series         | <a href="#">41792</a>                           |
| Application    | Power, Wire-to-Board                            |
| Overview       | <a href="#">KK® Interconnect System - Molex</a> |
| Product Name   | KK® 396                                         |
| UPC            | 800754201544                                    |

**Physical**


|                                |                           |
|--------------------------------|---------------------------|
| Breakaway                      | No                        |
| Circuits (Loaded)              | 12                        |
| Circuits (maximum)             | 12                        |
| Color - Resin                  | Natural                   |
| Durability (mating cycles max) | 25                        |
| Flammability                   | 94V-0                     |
| Glow-Wire Compliant            | No                        |
| Lock to Mating Part            | Yes                       |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Tin                       |
| Material - Resin               | Polyester                 |
| Net Weight                     | 5.721/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Right Angle               |
| PC Tail Length                 | 3.96mm                    |
| PCB Locator                    | No                        |
| PCB Retention                  | None                      |
| PCB Thickness - Recommended    | 1.60mm                    |
| Packaging Type                 | Bag                       |
| Pitch - Mating Interface       | 3.96mm                    |
| Polarized to Mating Part       | Yes                       |
| Polarized to PCB               | No                        |
| Shrouded                       | Partial                   |
| Stackable                      | Yes                       |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface: Style   | Through Hole              |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 7.0A |
| Voltage - Maximum             | 250V |

**Solder Process Data**

|                                                |      |
|------------------------------------------------|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-freeProcess Capability                    | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 235  |



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per  
-ED/79/2015 (17  
December 2015)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[41792](#) Series

**Mates With**

[2139](#) KK® Crimp Housing, [41695](#) KK®  
Crimp Housing, [6442](#) KK® Crimp Housing,  
[2145](#) PCB Connector, [41815](#) PCB  
Connector, [3069](#) KK® Crimp Housing

**Material Info**

Old Part Number 41792-0012

**Reference - Drawing Numbers**

Product Specification PS-08-50  
Sales Drawing SDA-41792

This document was generated on 03/09/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**