

### General Information

Extended Product Type:	JSM Orion07
Product ID:	2TLA022310R0500
EAN:	7350024481983
Catalog Description:	JSM Orion07 - Kit for O1&O2 in Stand (6)
Long Description:	JSM Orion07 - Kit for mounting of Orion1 & Orion2 in Stand (6 brackets) - For light guards with a height from 1200 mm

### Categories

Products » Low Voltage Products and Systems » Control Products » Safety Products » Optical Safety Devices

### Ordering

EAN:	7350024481983
Minimum Order Quantity:	1 piece
Customs Tariff Number:	9031908590

### Dimensions

Product Net Width:	0 mm
Product Net Height:	0 mm
Product Net Depth:	0 mm
Product Net Weight:	0.344 kg

### Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	150 mm
Package Level 1 Height:	30 mm
Package Level 1 Length:	180 mm
Package Level 1 Gross Weight:	0.344 kg

### Additional Information

Product Main Type:	Orion Kit
Product Name:	Mounting accessory
Suitable For:	Orion1-4-14-120-B Orion1-4-14-135-B Orion1-4-14-150-B Orion1-4-14-120-E Orion1-4-14-135-E Orion1-4-14-150-E Orion1-4-30-120-B Orion1-4-30-135-B Orion1-4-30-150-B Orion1-4-30-120-E Orion1-4-30-135-E Orion1-4-30-150-E Orion1-4-14-165-B Orion1-4-14-180-B Orion1-4-14-165-E Orion1-4-14-180-E Orion1-4-30-165-B Orion1-4-30-180-B Orion1-4-30-165-E Orion1-4-30-180-E Orion2-4-K4-120-B Orion2-4-K4-120-E

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information:	N/A
Declaration of Conformity - CE:	NoDecNee

### Classifications

Object Classification Code:	U
-----------------------------	---

