

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190130030](#)
Status: **Active**
Overview: [Standard Quick-Disconnect Terminals](#)
Description: InsulKrimp™ Fully Insulated Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 14-16 AWG, Expanded Blue Insulator, Tape

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-011 \(PDF\)](#)
[Product Specification PS-19902-008 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E79133

General
Product Family Quick Disconnects
Series [19013](#)
Crimp Quality Equipment Yes
Insulated Fully
Overview [Standard Quick-Disconnect Terminals](#)
Product Name InsulKrimp™
Type Quick Disconnect
UPC 822350963268


Physical
Barrel Type Closed - Brazed
Color - Resin Blue
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Insulation Nylon (PA)
Lock to Mating Part No
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.256/g
Orientation Straight
Packaging Type Adhesive Tape on Reel
Polarized to Mating Part Yes
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating 105°C
Wire Insulation Diameter 4.04mm max.
Wire Size AWG 14, 16
Wire Size mm² 1.30-2.00

Electrical
Voltage - Maximum 600V AC

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Old Part Number BB-2318T

Reference - Drawing Numbers
Product Specification PS-19902-008, PS-19902-011



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per
-ED/79/2015 (17
December 2015)
Halogen-Free
Status
Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS Green Image
ELV Not Relevant

Search Parts in this Series
[19013](#) Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Mini-Mac™	0638852400
Applicator	
ATP Crimp Dies	0198132020
for the Tape Crimp	
Module and ATP-101	
& 301 Press	
Crimp Head for the	0640056300
AT-200™ Pneumatic	
Hand Tool	
Hand Crimp Tool	0640016300

This document was generated on 03/04/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION