

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191600012](#)
Status: **Active**
Overview: [Splices](#)
Description: Closed-End Insulated Splice for 14-22 AWG Wire, Clear

Documents:

Drawing (PDF)	Packaging Specification PK-19408-109 (PDF)
Product Specification PS-19902-013 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Splices
Series	19160
Crimp Quality Equipment	Yes
Mil-Spec	N/A
MolexKits	Yes
Overview	Splices
Product Name	Closed-End Insulated
UPC	800753110229

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.472/g
Packaging Type	Bag
Temperature Range - Operating	105°C
Wire Insulation Diameter	6.10mm max.
Wire Size AWG	14, 16, 18, 20, 22

Electrical

Voltage - Maximum	300V
-------------------	------

Material Info

Old Part Number	NC-2214
-----------------	---------

Reference - Drawing Numbers

Packaging Specification	PK-19408-109
Product Specification	PS-19902-013
Sales Drawing	SD-19160-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19160](#) Series

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
Hand Crimp Tool	0640010600
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050600
Crimp Head for the AT-200™ Pneumatic Hand Tool, Crimp from Top	0640053400

This document was generated on 08/08/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION