


CAMBLOCK

5mm Pitch Double Decker Rising Clamp Terminal

PCB
TERMINAL
BLOCKS

- 4(2x2) & 6(2x3) pole double interlocking mechanism for increased strength
- Double decker
- Moulded in green UL94-V0 flame retardant PA
- Professional rising clamp terminals
- 0.3-3.3 mm² (22-12 AWG)
- Guided pin alignment
-  us approved

CTBDD2VG



TYPE NO.	POLES	LENGTH
CTBDD2VG/2	4	12.5mm
CTBDD2VG/3	6	17.5mm

SPECIFICATION

Rating	10A/300V
Insulation Resistance	5000MΩ/1000V
Withstand Voltage	AC2000V/1min
Working temperature	-33°C to +120°C
Moulding	UL94-V0 flame retardant PA
Pin/terminal	Tinned, nickel plated brass
Wire clamp	Nickel plated brass
Screw/torque	M2.5 steel, zinc plated 0.5Nm
Recommended PCB hole size	ø1.3mm

