


### 3 Watt

- Regulated Single & Dual Output
- 2:1 Input Range
- Compact DIP8 Package
- 1500 VDC Isolation
- Operating Temperature -40 °C to +95 °C
- ITE Safety Approvals
- Full Load at 70 °C
- Class A Conducted & Radiated Emissions
- 3 Year Warranty



#### Dimensions:

##### IEU03:

0.55 x 0.55 x 0.31" (14.0 x 14.0 x 8.0 mm)

### Models & Ratings

Input voltage	Output voltage	Output current	Input current <sup>(1)</sup>		Maximum capacitive load <sup>(2)</sup>	Efficiency	Model number
			No load	Full load			
4.5-10V	3V3	600 mA	45 mA	500 mA	100 µF	79%	IEU0305S3V3
	5 V	600 mA		740 mA	100 µF	81%	IEU0305S05
	12V	250 mA		705 mA	100 µF	85%	IEU0305S12
	15V	200 mA		705 mA	100 µF	85%	IEU0305S15
	±5V	±300 mA		770 mA	±100 µF	82%	IEU0305D05
	±12V	±125 mA		715 mA	±100 µF	84%	IEU0305D12
	±15V	±100 mA		705 mA	±100 µF	85%	IEU0305D15
	9-18V	3V3		600 mA	27 mA	205 mA	100 µF
5 V		600 mA	300 mA	100 µF		83%	IEU0312S05
12V		250 mA	285 mA	100 µF		87%	IEU0312S12
15V		200 mA	285 mA	100 µF		87%	IEU0312S15
±5V		±300 mA	300 mA	±100 µF		84%	IEU0312D05
±12V		±125 mA	290 mA	±100 µF		86%	IEU0312D12
±15V		±100 mA	285 mA	±100 µF		87%	IEU0312D15
18-36V		3V3	600 mA	16 mA		105 mA	100 µF
	5 V	600 mA	150 mA		100 µF	83%	IEU0324S05
	12V	250 mA	145 mA		100 µF	87%	IEU0324S12
	15V	200 mA	145 mA		100 µF	87%	IEU0324S15
	±5V	±300 mA	150 mA		±100 µF	84%	IEU0324D05
	±12V	±125 mA	145 mA		±100 µF	86%	IEU0324D12
	±15V	±100 mA	145 mA		±100 µF	87%	IEU0324D15
	36-75V	3V3	600 mA		10 mA	52 mA	100 µF
5 V		600 mA	76 mA	100 µF		82%	IEU0348S05
12V		250 mA	73 mA	100 µF		86%	IEU0348S12
15V		200 mA	73 mA	100 µF		86%	IEU0348S15
±5V		±300 mA	76 mA	±100 µF		82%	IEU0348D05
±12V		±125 mA	74 mA	±100 µF		85%	IEU0348D12
±15V		±100 mA	74 mA	±100 µF		85%	IEU0348D15

### Notes

1. Input currents measured at nominal input voltage.
2. Maximum capacitive load is per output.

### Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	4.5		10	VDC	5 V nominal
	9.0		18		12 V nominal
	18.0		36		24 V nominal
	36.0		75		48 V nominal
Input Filter	Internal Capacitor				
Input Surge			12	VDC for 1 s	5 V nominal
			25		12 V nominal
			50		24 V models
			100		48 V models

### Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	3.3		30	VDC	See Models and Ratings table
Initial Set Accuracy			±1.5	%	At full load
Output Voltage Balance			±2.0	%	For dual output with balanced loads
Minimum Load				A	No minimum load required
Line Regulation			±0.2	%	From minimum to maximum input at full load
Load Regulation			±1.0	%	From 0 to full load
Cross Regulation			±5.0	%	On dual output models when one load is varied between 25% and 100% and other is fixed at 100%
Transient Response			5	% deviation	Recovery within 1% in less than 500 µs for a 25% load change.
Ripple & Noise		70		mV pk-pk	20 MHz bandwidth. Measured using 0.47 µF ceramic capacitor.
Overload Protection		170		%	
Short Circuit Protection					Continuous, with auto recovery
Maximum Capacitive Load					See Models and Ratings table
Temperature Coefficient			0.02	%/°C	

### General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		84		%	See Models and Ratings table
Isolation: Input to Output	1500/1800			VDC	60 s/1 s
Isolation Resistance	10 <sup>9</sup>			Ω	At 500 VDC
Isolation Capacitance		100		pF	
Switching Frequency		100		kHz	
Power Density			32.0	W/in <sup>3</sup>	
Mean Time Between Failure		3.4		MHrs	MIL-HDBK-217F, +25 °C GB
Weight		0.008 (3.9)		lb (g)	

### Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-40		+95	°C	See Derating Curve.
Storage Temperature	-50		+125	°C	
Case Temperature			+95	°C	
Humidity			95	%RH	Non-condensing
Cooling					Natural convection
Case Flammability	UL 94V-0 Rated				Non conductive black plastic
Lead-Free Reflow Solder Process					IPC/JEDEC J-STD-020D.1

### EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55022	Class A	See application note
Radiated	EN55022	Class A	See application note


### EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ESD	EN61000-4-2	±8 kV air discharge, ±6 kV contact	A	
Radiated	EN61000-4-3	10 V/m	A	
EFT/Burst	EN61000-4-4	±2 kV	A	With external input capacitor, suggested part is CHEMI-CON KY 220µF/100V
Surge	EN61000-4-5	±1 kV	A	With external input capacitor, suggested part is CHEMI-CON KY 220µF/100V
Conducted	EN61000-4-6	3 V rms	A	
Magnetic Fields	EN61000-4-8	3 A/m	A	

### Safety Approvals

Safety Agency	Safety Standard	Notes & Conditions
CB Report	IEC60950-1	Information Technology
UL	UL/cUL60950-1	Information Technology

### Mechanical Details




Pin Connections		
Pin	Single	Dual
1	-Vin	-Vin
4	+Vin	+Vin
5	+Vout	+Vout
6	No Pin	Common
7	-Vout	-Vout

### Notes


- All dimensions are in inches (mm)
- Weight: 0.008 lbs (3.9 g) approx.
- Tolerance: X.XX±0.01 (X.X±0.25)  
X.XXX±0.005 (X.XX±0.13)
- Pin Tolerance: ±0.002 (±0.05)

### Application Notes

#### Derating Curve



#### EMI Filter



Model	C1	L1
IEU0205	22 µF/16 V	3.3 µH
IEU0212	22 µF/25 V	18.0 µH
IEU0224	10 µF/50 V	39.0 µH
IEU0248	3.3 µF/100 V	68.0 µH

C1 = 5, 12 & 24 V: 1206 X5R MLCC, 48 V: 1206 X7S MLCC, L1 = SCD0504T series