

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0561348100**  
**Status:** **Active**  
**Overview:** MicroClasp™ Wire-to-Board System  
**Description:** 2.00mm Pitch Crimp Terminal 56134, Female, 22-26 AWG, Bag, Phosphor Bronze, for 51242/51353/51382 Housings

**Documents:**

[3D Model](#) [Packaging Specification SPK-56134-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Application Specification 5055960001 \(PDF\)](#)

**General**

Product Family Crimp Terminals  
Series [56134](#)  
Application Signal  
Crimp Quality Equipment Yes  
Overview [MicroClasp™ Wire-to-Board System](#)  
Product Name MicroClasp™  
UPC 800756190549


**Physical**

Gender Female  
Material - Metal Phosphor Bronze  
Material - Plating Mating Tin  
Material - Plating Termination Tin  
Net Weight 36.000/mg  
Packaging Type Bag  
Plating min - Mating 0.889µm  
Plating min - Termination 0.914µm  
Termination Interface: Style Crimp or Compression  
Wire Insulation Diameter 1.25-1.70mm  
Wire Size AWG 22, 24, 26  
Wire Size mm² N/A

**Material Info**

**Reference - Drawing Numbers**

Application Specification 5055960001  
Packaging Specification SPK-56134-001  
Product Specification RPS-51353-016, RPS-51382-015  
Sales Drawing SD-56134-002



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[56134 Series](#)

**Use With**

[51242 Dual Row Crimp Housing](#), [51353 Dual Row Crimp Housing](#), [51382 Single Row Crimp Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Insertion Tool	<a href="#">0011020022</a>
Hand Crimp Tool	<a href="#">0638116300</a>
Extraction Tool	<a href="#">0638132700</a>

**Japan**

Description	Product #
-------------	-----------

This document was generated on 08/15/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**