

Projector C205

Ideas in your pocket

- iF Design Award 2015.
- The pocket size makes it ideal for business and personal use.
- Great companion for smartphone.
- Two built in speakers provide powerful sound.
- Wireless Projection¹ frees you from cable.
- Long LED lifespan up to 30,000 hours.



* Wireless Projection only works along with optional Acer wireless dongle

Product Specifications

Model name	Acer C205
Projection system	DLP®
Native Resolution	Native FWVGA (854 x 480) Maximum WXGA (1,280 x 800)
Aspect ratio	16:9 (Native), 4:3
Throw Ratio	82" @ 2m (1.1:1)
Contrast ratio	1,000:1
Brightness	200 ANSI lumens (standard), 160 ANSI lumens (ECO)
LED life	20,000 hours (standard), 30,000 hours (ECO)
Projection lens	F = 1.8, f = 7.18 mm, Manual Focus
Keystone correction	NA
Noise level	29 dBA (standard), 25 dBA (ECO)
Input interface	1x HDMI®/MHL™ (video, audio, HDCP) 1x PC audio (stereo mini jack)
Output interface	1x DC Out (5V/1A, USB Type A)
Speakers	4W stereo (2W x2) speakers
Dimensions	144 x 108 x 27 mm
Weight	302 g

Feature Highlights

A pocket size ideal for both business and personal use

- Less than 0.3 Kg – extremely light and slim
- FWXGA (854 x 480) resolution
- 200 lumens
- 30,000 hours LED lamp life maintains consistent display performance

Act as a portable power bank with smartphone

- Built-in battery for cable-free, long time lasting usage
- MHL connectivity
- Power Bank extends operating time


Enable wireless projection¹

- Mirror display via Miracast™
- HDMI® digital connectivity

Enhanced audio performance

- Built-in a powerful 4W stereo speakers

* Wireless Projection only works along with optional Acer wireless dongle.



iF Design Award 2015

Organized by the International Forum Design of Germany, the iF award logo has become synonymous for outstanding design around the world since 1953. Winning this coveted award reflects the jury's recognition for outstanding achievements in design quality, finish, choice of materials, degree of innovation, environmental impact, functionality, as well as universal design.



MHL™ Connectivity

With the MHL connectivity, the projector is capable of performing the uncompressed HDMI digital signals and multi-channel audio from an MHL supported smartphone. The charging capability from projector to the battery of smartphone is also provided. Furthermore, with the Acer unique MHL wireless adapter attaching to the MHL™/HDMI™ port, the projector can display the content wirelessly from a PC, Tablet, Smartphone or Set-Top Box with Miracast or DLNA WiFi Display capability.

Instant On/Off

With the LED light source, users can enjoy the big screen display immediately as soon as the projector is turned on, just like turning on a TV. Unlike a lamp based projector, waiting the warm-up of the device is no longer required for a LED based projector. The Instant Off is also achievable by the LED light source. User can turn off the projector then unplug the power cord immediately without any concern for damaging



Acer EcoProjection

Acer EcoProjection is a complete environment-friendly power management solution that reduces standby power consumption by up to 90%, from 5 W to 0.5 W. Also featured in the Acer EcoProjection suite is Acer ePower Management for customized power-saving configurations.

About Acer

Established in 1976, Acer is an information and communication technology company dedicated to the research, design, marketing, sale and support of innovative products that enhance people's lives. Acer's green supply chain delivers environmentally friendly PCs, displays, projectors, servers, tablets and smartphones – tools our customers need to explore beyond limits and experience more. Ranked No. 3 for notebooks globally (IDC 2012), Acer employs 8,000 people, and 2012 revenues reached US\$14.7 billion. Please visit www.acer.com for more information.

