

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008520071](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, Tin \(Sn\)](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	2478
Application	Power
Crimp Quality Equipment	Yes
Overview	KK® Interconnect System - Molex
Packaging Alternative	08-52-0072 (Loose)
Product Name	KK® 396, KK® 508
UPC	800753758131

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.240/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.79mm max.
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2478-3-(P909)
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-2478
---------------	---------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[2478](#) Series

Use With

[2574](#) , [2139](#) , [41695](#) , [3069](#) , [6422](#) , [5265](#) ,
[5239](#)