

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191930212](#)
Status: **Active**
Overview: [VersaKrimp™ Terminals and Splices](#)
Description: [VersaKrimp™ Ring Tongue Terminal for 6 AWG Wire](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19193](#)
 Crimp Quality Equipment Yes
 Mil-Spec N/A
 Overview [VersaKrimp™ Terminals and Splices](#)
 Product Name VersaKrimp™
 Type Ring
 UPC 800755050615

Physical


Barrel Type Closed - Brazed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 6.133/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Stud Size 1/4" (M6)
 Termination Interface: Style Crimp or Compression
 Wire Size AWG 6

Material Info

Old Part Number E-357-14

Reference - Drawing Numbers

Sales Drawing SD-19193-015



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[19193 Series](#)

Application Tooling | [FAQ](#)

*Tooling specifications and manuals are
 found by selecting the products below.
 Crimp Height Specifications are then
 contained in the Application Tooling
 Specification document.*

Global

Description	Product #
Hydraulic Dieless Crimping Tool	0638161700
Die Set (large) for the HHLS Hydraulic Crimper	0192900004
Manual Putt Pump Hydraulic System, Die set required	0192860117
Square "DIN" style dies for 6 AWG	0640037770

Hand Crimp Tool 0640013900
Crimp Head for the 0640074300
AT-200™ Pneumatic
Hand Tool

This document was generated on 07/18/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION