

# Product information

## 10.8v CXT Drill Driver



### DF331DWAE

Voltage	10.8 v
Max. in wood	21 mm
Max. in steel	10 mm
Torque Settings	18+ drill
Torque Settings; S/H Nm	14/30
Battery Type	Lithium-ion
Battery Quantity (2.0Ah)	2
Vibration: Drilling	2.5 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Noise sound pressure	70 dB(A)
Noise K factor	3 dB(A)
Net weight	1.3 kg
Chuck Capacity	0.8 – 10 mm
No Load Speed (Hi)	0 - 1,700 rpm
No Load Speed (Lo)	0 - 450 rpm



LITHIUM-ION



**STANDARD EQUIPMENT:** 197394-3 Battery BL1020B , DC10WC 10.8V Charger

- Slide type Li-ion battery
- Electric brake
- 2 mechanical gears.
- Variable speed control trigger.
- Keyless Chuck
- Equipped with Battery protection circuit: designed to protect the battery from damages due to overdischarge, high temperature or overload current.
- Forward and reverse trigger.
- LED job light
- Ergonomic soft grip

Details correct as of: 15-9-2016

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)