




THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.




| REVISIONS | | | |
|-----------|--|----------|-----------|
| REV | DESCRIPTION | DATE | APPROVED |
| B | REVISED ADDED LOGO (ECN# 1291) | 01/20/03 | MCCORMICK |
| C | ECN#1605 ADDED COMPONENT SPECIFICATION TABLE | 12/15/03 | MCCORMICK |
| D | ECN# 1962 REVISED TOLERANCE & MODIFIED COMPONENT SPECIFICATION | 01/26/05 | MCCORMICK |
| E | ECN# 2294 REVISED TOLERANCE TO ONE PLACE | 01/18/06 | MCCORMICK |



SERIES "A" USB JACK
J1



SERIES "A" USB JACK
J2



| TABLE | |
|-------|-------|
| J1 | J2 |
| PIN 1 | PIN 1 |
| PIN 2 | PIN 2 |
| PIN 3 | PIN 3 |
| PIN 4 | PIN 4 |
| GRD | GRD |

| Component Specifications | |
|--------------------------|-------------------------|
| Material | |
| Overmold | PVC |
| Contacts | Brass |
| Insulator | PBT, UL 94V-0 |
| Finish | |
| Shell | Nickel Silver |
| Contacts | Gold over Nickel |
| Electrical | |
| Current Rating | 3 Amp |
| Dielectric Strength | 1000V AC for one minute |
| Insulator Resistance | 1000Ω min at 500V DC |
| USB 2.0 Compliant | |

CS-155

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES
TOLERANCES ARE:
X ±.1
XX ±.05
XXX ±.005
CABLE LENGTH TOLERANCE
<300" ±5% >300" ±2%

| APPROVALS | DATE |
|--------------------------|------------|
| DRAWN BY C.MCCORMICK | 12/20/2002 |
| CHECKED BY D.PARHAM | 12/20/2002 |
| APPROVED BY R.CARRICK | 12/20/2002 |

CONFIGURATION DETAILS OF
UNDIMENSIONED FEATURES
MAY VARY

| | | | |
|---|--------------------------|--|------------------|
| | | 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845 | |
| PRODUCT DESCRIPTION SERIES "A" JACK TO SERIES "A" JACK ADAPTOR | | | |
| DRAWING TITLE <h2 style="text-align: center;">OUTLINE DRAWING</h2> | | | |
| SIZE A | FSCM NO. 43321 | DWG. NO. UAD015FF-OD1 | REV. E |
| SCALE: NONE CAD FILE: UAD015FF-OD1.SLDDRW SHEET 1 OF 1 | | | |